For closing pre-threaded holes
Assembling with screwdriver



Corrosion-resistant

Robust

Reliability

Temperature-resistant

Application range
Machine and equipment manufacturing
Electric motor manufacturing

Design
Metric connection thread acc. to EN 50262

Remark
Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	63 x 1,5
Outer Ø (mm):	70
Pieces / PU:	10
On request:	Fitted with FKM O-ring
Material:	Body: nickel-plated brass Sea water-resistant
Protection rating:	IP 54 IP 68 with O-ring
Temperature range:	With O-ring: -30°C to +100°C Without O-ring: -60°C to +200°C

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.



PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.