

DATA SHEET	52103405
SKINDICHT® BL-M hex.	valid from 28.10.2008

SKINDICHT® BL-M hexagonal brass blind plugs with metric thread in acc. with EN 50262 for ensuring the protections class for unused threaded holes, incl. O-Ring



Components:

Body: Messing vernickelt
O-Ring: NBR
(on request Viton® O-Ring)

Technical Feature:

Connection thread: M12x1,5 up to M63x1,5 in acc. to DIN 60423
Protection class: IP 68 5bar, test in acc. to DIN 60 529
Temperature range: -30 up to +100°C

Part Number	Part designation/size	wrench-size	outer Ø
5210 3405	SKINDICHT BL-M 6kt. 12x1,5	16	17,8
5210 3415	SKINDICHT BL-M 6kt. 16x1,5	20	22,0
5210 3425	SKINDICHT BL-M 6kt. 20x1,5	24	26,4
5210 3435	SKINDICHT BL-M 6kt. 25x1,5	29	31,9
5210 3445	SKINDICHT BL-M 6kt. 32x1,5	36	39,6
5210 3455	SKINDICHT BL-M 6kt. 40x1,5	45	49,5
5210 3465	SKINDICHT BL-M 6kt. 50x1,5	54	59,0
5210 3475	SKINDICHT BL-M 6kt. 63x1,5	67	73,5

For more information please see our current catalogue.
Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.