

U.I. Lapp GmbH	DATASHEET	
	SKINDICHT® BL-M	52103190 14.11.2013

For closing pre-threaded holes
Assembling with screwdriver



Corrosion-resistant



Robust



Reliability



Temperature-resistant

Application range

Machine and equipment manufacturing
Electric motor manufacturing

Design

Metric connection thread acc. to EN 50262

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	75 x 1,5
Outer Ø (mm):	80
Pieces / PU:	1
On request:	Fitted with FKM O-ring
Material:	Body: nickel-plated brass Sea water-resistant
Protection rating:	IP 54 IP 68 with O-ring
Temperature range:	With O-ring: -30°C to +100°C Without O-ring: -60°C to +200°C

Product Management	Document: SKINDICHT® BL-M	1 / 2
--------------------	---------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® BL-M	52103190 14.11.2013



Product Management	Document: SKINDICHT® BL-M	2 / 2
--------------------	---------------------------	-------