

DATA SHEET	52103103
SKINDICHT® BL-M ATEX	valid from : 21.04.2011

SKINDICHT® BL-M ATEX nickel plated brass blind plug with guiding notch for O-Ring (recess) and metric connection thread acc.to EN 50262 for ensuring the protection class for existing thread holes which are not use.



Component parts:

Body: nickel plated brass
O-Ring: NBR

Technical feature:

Connecting thread: M12x1.5 up to M63x1.5 in acc. to EN 60423
Protection class: IP66 and IP 68 / 5 bar, in acc. to EN 60 529
Temperature range: -30 up to +90°C

Applications range:

Equipment Group II / Category 2G + 1D
Devices, machines and marine applications
Chemical and petrochemical industry

Approvals:



Norm references:



Part number	Type Size M	Thread length	Wrench size	Outer Ø
5210 3103	SKINDICHT BL-M ATEX 12x1.5	5	16	17.8
5210 3113	SKINDICHT BL-M ATEX 16x1.5	5	20	22.0
5210 3123	SKINDICHT BL-M ATEX 20x1.5	6	24	26.4
5210 3133	SKINDICHT BL-M ATEX 25x1.5	7	29	31.9
5210 3143	SKINDICHT BL-M ATEX 32x1.5	8	36	39.6
5210 3153	SKINDICHT BL-M ATEX 40x1.5	8	45	49.5
5210 3163	SKINDICHT BL-M ATEX 50x1.5	9	54	59.0
5210 3173	SKINDICHT BL-M ATEX 63x1.5	10	67	73.5

EC Type Examination Certification IBExU 03 ATEX 1011

For more information please see our current catalogue.

Please do not hesitate to contact our laboratory if there any questions regarding resistance against aggressive agents and special oil.