

U.I. Lapp GmbH	DATASHEET	
	SKINDICHT® BL-M ATEX	52103143 14.11.2013

High degree of protection
Cold impact resistance



Corrosion-resistant



Robust



Reliability



Temperature-resistant

Application range

Equipment group II / Category 2G+1D
Devices, machines and apparatus
For mobile applications in offshore and marine industries
Chemical and petrochemical industry

Design

Metric connection thread acc. to EN 50262

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	32 x 1,5
SW (mm):	36
Thread length, D (mm):	8
Outer Ø (mm):	39,6
PU:	25
Approvals:	CE 0637 Ex II 2G Ex eb IIC Ex II 1D Ex ta IIIC IECEx IBE 13.0029X
Material:	Body: nickel-plated brass O-ring: NBR
Protection rating:	IP 68
Temperature range:	-30 °C to +90 °C

Product Management	Document: SKINDICHT® BL-M ATEX	1 / 1
--------------------	--------------------------------	-------