

U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINDICHT® DTN</b>	<b>52105040</b> <b>14.11.2013</b>

Can be used as multiple-duct sleeve  
Strain relief



Optimum strain relief

#### Application range

Grommets for cables from 4 to 32 mm cable diameter.

#### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

#### Technical Data

Article designation / size:	DTN 3
Clamping range ØF (mm):	12 - 17,5
Metal thickness (mm):	2,5
Hole in housing Ø (mm):	25
Sleeve inner Ø (mm):	18
Pieces / PU:	50
Colour delivered:	Black
Material:	CR
Temperature range:	-30°C to +100°C

Product Management	Document: SKINDICHT® DTN	1 / 1
--------------------	--------------------------	-------