

DATA SHEET	52008010
SKINDICHT® FL	valid from : 30.10.2008

The SKINDICHT® FL is a variable flange; it can be used universally for flat or round cables. It is mainly used for large flat cables which cannot be accommodated in our SKINDICHT® flat cable glands, up to PG 48. Several flat cables can also be fed through at the same time. If several round cables have to be fed through an extremely narrow space, the solid seal is drilled out accordingly. The seal profiles enable to solve many problems. Through the conical internal contour in the upper part of the housing the sealing inserts are pressed on to the cable. Applications fields are for example crane building, plant construction, for power chains and restricted spaces.



Components:

Body:	Aluminium- Special untreated alloy
Screws and spring washers:	Zink plated steel
Seal:	Perbunan

Technical Features:

Sizes:	FL 1 – FL 5
Protection class:	IP 65, test in acc. to EN 60 529
Temperature range:	- 20° C up to + 100° C

For more information please see our current catalogue.
Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.