

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® JT PTFE metric	53801040 14.11.2013

Resistant to oil, water, alkaline solutions, acids, solvents, etc.
Suitable for foodstuffs



Good chemical resistance



Food & Beverage



Acid-resistant



Temperature-resistant

Application range

PTFE sealing disks for SKINTOP® and SKINDICHT® cable glands

Note

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	JT M 16
Inner Ø (mm):	16,1
Thickness (mm):	2
Outer Ø (mm):	21,1
Pieces / PU:	100
Colour delivered:	White
Material:	PTFE
Temperature range:	-120°C to +250°C Short-term: up to +300°C

Product Management	Document: SKINDICHT® JT PTFE metric	1 / 1
--------------------	-------------------------------------	-------