


U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINDICHT® JT PTFE metric</b>	<b>53801100</b> <b>14.11.2013</b>

Resistant to oil, water, alkaline solutions, acids, solvents, etc.  
Suitable for foodstuffs



Good chemical resistance



Food & Beverage



Acid-resistant



Temperature-resistant

#### Application range

PTFE sealing disks for SKINTOP® and SKINDICHT® cable glands

#### Note

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

#### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

#### Technical Data

Article designation / size:	JT M 63
Inner Ø (mm):	63,2
Thickness (mm):	3
Outer Ø (mm):	73,9
Pieces / PU:	25
Colour delivered:	White
Material:	PTFE
Temperature range:	-120°C to +250°C Short-term: up to +300°C

Product Management	Document: SKINDICHT® JT PTFE metric	1 / 1
--------------------	-------------------------------------	-------