

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® MR-M	52104321 14.11.2013

Enables the use of cable glands with smaller connection threads than the existing threaded holes



Space requirement



Reliability



Connector with standard housing unit



Application range

Machines
Devices
Housings

Design

Metric connection thread acc. to EN 50262

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Thread, male M1:	63 x 1.5
Thread, female M2:	40 x 1.5
Pieces / PU:	10
On request:	Also available with pre-installed O-ring
Material:	Nickel-plated brass
Temperature range:	-60°C to +200°C

Product Management	Document: SKINDICHT® MR-M	1 / 1
--------------------	---------------------------	-------