Enables the use of cable glands with smaller connection threads than the existing threaded holes
With guide notch for O-ring
Assembling with a wrench



Space requirement

Application range
Machines
Devices
Housings

Design
Metric connection thread acc. to EN 50262


Remark
Viton® is a registered trademark of DuPont de Nemours
Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Thread, male M1:	32 x 1.5
Thread, female M2:	20 x 1.5
SW (mm):	36
ØA [mm]:	40
Overall length, C (mm):	11,5
Thread length, D (mm):	8
Pieces / PU:	25
On request:	VITON® O-ring -20 °C to +200 °C
Material:	Body: nickel-plated brass O-ring: NBR
Temperature range:	-30°C to +100°C

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.





PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.