

U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINDICHT® O-Ring Perbunan® metric</b>	53102021 14.11.2013



UV-resistant

### Application range

For sealing the housing reliably to protect against oils, dust, and water at the connection thread of a gland or other similar parts

### Note

O-rings with thickness of 1.5 mm are recommended for optimum sealing of the converter SKINDICHT® ZSE-M12/16/20 x 1.5  
Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

### Remark

Perbunan® is a registered trademark of BAYER AG

Photographs are not to scale and do not represent detailed images of the respective products.

### Technical Data

Article designation / size:	O M 20 x 1,5
Inner Ø (mm):	17
Cable thickness (mm):	1.5
Pieces / PU:	100
Colour delivered:	Black
Material:	NBR Ozone and UV-resistant silicone-free
Temperature range:	-30°C to +100°C

Product Management	Document: SKINDICHT® O-Ring Perbunan® metric	1 / 1
--------------------	--	-------