

U.I. Lapp GmbH	DATASHEET	
	SKINDICHT® O-Ring Perbunan® metric	53102050 14.11.2013



UV-resistant

Application range

For sealing the housing reliably to protect against oils, dust, and water at the connection thread of a gland or other similar parts

Note

O-rings with thickness of 1.5 mm are recommended for optimum sealing of the converter SKINDICHT® ZSE-M12/16/20 x 1.5
Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Remark

Perbunan® is a registered trademark of BAYER AG

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	O M 40 x 2,0
Inner Ø (mm):	36
Cable thickness (mm):	2
Pieces / PU:	50
Colour delivered:	Black
Material:	NBR Ozone and UV-resistant silicone-free
Temperature range:	-30°C to +100°C

Product Management	Document: SKINDICHT® O-Ring Perbunan® metric	1 / 1
--------------------	--	-------