

U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINDICHT® O-ring VITON® metric</b>	52122070 14.11.2013



Good chemical resistance



Acid-resistant



Temperature-resistant

### Application range

For sealing the housing reliably to protect against oils, acids, and chemicals at the connection thread of a gland or other similar parts under extreme conditions

### Note

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

### Remark

Viton® is a registered trademark of DuPont de Nemours

Photographs are not to scale and do not represent detailed images of the respective products.

### Technical Data

Article designation / size:	OV M 63 x 2,0
Inner Ø (mm):	57
Cable thickness (mm):	2
Pieces / PU:	25
Colour delivered:	Green
Material:	FKM
Temperature range:	-20 °C to +200 °C

Product Management	Document: SKINDICHT® O-ring VITON® metric	1 / 1
--------------------	---	-------