

U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINDICHT® O-Ring Perbunan® PG</b>	52005770 14.11.2013

Resistant to oil, dust and water



UV-resistant

### Application range

For a reliable sealing against foreign objects and liquids at the connecting thread of a gland or similar components.

### Note

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

### Remark

Perbunan® is a registered trademark of BAYER AG

Photographs are not to scale and do not represent detailed images of the respective products.

### Technical Data

Article designation / size:	O 48
Inner Ø x thickness Ø (mm):	55 x 2
Pieces / PU:	50
Colour delivered:	Black
Material:	NBR Ozone and UV-resistant
Temperature range:	-20°C to +100°C

Product Management	Document: SKINDICHT® O-Ring Perbunan® PG	1 / 1
--------------------	------------------------------------------	-------