



DATA SHEET	52004180
SKINDICHT® RWV	valid from : 23.05.2003

The SKINDICHT® RWV a cast zinc cable gland with 90°elbow. The locknut enables the angle gland to be secured in any position.



The gland make-up consists of:

Angle housing	cast zinc
Washer	galvanized steel
Pressure screw	nickel-plated brass
Locknut	nickel-plated brass
Indented sealing ring	elastomer
O – ring	elastomer

Technical features:

Connecting thread:	PG 7- PG 29 in accordance to DIN 40 430
IP protection:	IP 55 in acc. to DIN 40 050
Temperature range:	- 20°C to + 80°C

For more information please see our current catalogue.
Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

elaborated by: TE-VZ: R. Drotleff	Document: DB52004180EN	page 1 of 1
--------------------------------------	------------------------	-------------