



<b>DATA SHEET</b>	52004130
<b>SKINDICHT® SE</b>	valid from : 31.10.2008

The SKINDICHT® SE flange angle gland, characterised by design, exceptionally low overall height and stability. It can be securely and shortly installed with only two or four fixing holes. The recessed Perbunan® O-ring guarantees a strong seal between the housing and the gland. The die cast zinc material is resistant against tropical conditions and corrosion, even in combination with grey cast iron or steel. The SKINDICHT® SE flange angle can be combined with all special cable glands in our range such as sealing-, strain-relieve-, bending protection-, conduit connection- or earthing glands. The protection class depends on the special glands which are combined, but the standard version minimum IP 55.



#### Components:

Body:	cast zinc, grey, hammertone enamelled
Flat washer:	zinc plated steel
Compression screw:	nickel plated brass
Incised sealing ring:	elastomer
Sleeve:	PE
O-Ring:	elastomer

#### Technical Feature:

Connection thread:	PG 16 up to PG 36 in acc. to DIN 40 430
Temperature range:	SE 16 – SE 36 - 20° C up to + 80° C
Protection class:	IP 55
Surface:	structured finish, colour RAL 7001

For more information please see our current catalogue.  
Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.