

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® SE-M	52108010 14.11.2013

Sealed by incised sealing ring
Corrosion-resistant
Easy to install
Completely safe cable entry
Low overall height



Corrosion-resistant



Mechanical resistance



Space requirement



Connector with standard housing unit



Temperature-resistant

Application range

For high mechanical stress
When no connection thread is provided

Design

M20 x 1.5 - M25 x 1.5 with 2 screw holes
M32 x 1.5 with 4 screw holes
With incised sealing ring

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINDICHT® SE-M	1 / 2
--------------------	---------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® SE-M	52108010 14.11.2013

Technical Data

Article designation / size:	M 25 x 1,5
Incised sealing ring ØF (mm):	8.5/11.5/14.5/17.5
Overall height (mm):	40
SW (mm):	25
Overall length, C (mm):	68,2
Overall width (mm):	60
Pieces / PU:	5
Material:	Body: zinc die-casting, grey, hammer tone finish Compression screw: nickel-plated brass Incised sealing ring: CR/NBR O-ring: NBR
Protection rating:	IP 55
Temperature range:	-20°C to +80°C

Product Management	Document: SKINDICHT® SE-M	2 / 2
--------------------	---------------------------	-------