

|                   |                        |                                                                                                      |
|-------------------|------------------------|------------------------------------------------------------------------------------------------------|
| U.I. Lapp<br>GmbH | <b>DATASHEET</b>       |  <b>LAPP GROUP</b> |
|                   | <b>SKINDICHT® SE-M</b> | <b>52108020</b><br><b>14.11.2013</b>                                                                 |

Sealed by incised sealing ring  
Corrosion-resistant  
Easy to install  
Completely safe cable entry  
Low overall height



Corrosion-resistant



Mechanical resistance



Space requirement



Connector with standard housing unit



Temperature-resistant

#### Application range

For high mechanical stress  
When no connection thread is provided

#### Design

M20 x 1.5 - M25 x 1.5 with 2 screw holes  
M32 x 1.5 with 4 screw holes  
With incised sealing ring

#### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

|                    |                           |       |
|--------------------|---------------------------|-------|
| Product Management | Document: SKINDICHT® SE-M | 1 / 2 |
|--------------------|---------------------------|-------|

|                   |                        |                                                                                                      |
|-------------------|------------------------|------------------------------------------------------------------------------------------------------|
| U.I. Lapp<br>GmbH | <b>DATASHEET</b>       |  <b>LAPP GROUP</b> |
|                   | <b>SKINDICHT® SE-M</b> | <b>52108020</b><br><b>14.11.2013</b>                                                                 |

#### Technical Data

|                               |                                                                                                                                              |
|-------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------|
| Article designation / size:   | M 32 x 1,5                                                                                                                                   |
| Incised sealing ring ØF (mm): | 16/19/22/25                                                                                                                                  |
| Overall height (mm):          | 51.5                                                                                                                                         |
| SW (mm):                      | 32                                                                                                                                           |
| Overall length, C (mm):       | 84,2                                                                                                                                         |
| Overall width (mm):           | 66                                                                                                                                           |
| Pieces / PU:                  | 1                                                                                                                                            |
| Material:                     | Body: zinc die-casting, grey,<br>hammer tone finish<br>Compression screw: nickel-plated brass<br>Incised sealing ring: CR/NBR<br>O-ring: NBR |
| Protection rating:            | IP 55                                                                                                                                        |
| Temperature range:            | -20°C to +80°C                                                                                                                               |

|                    |                           |       |
|--------------------|---------------------------|-------|
| Product Management | Document: SKINDICHT® SE-M | 2 / 2 |
|--------------------|---------------------------|-------|