

U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINDICHT® SHV cone seal</b>	52021271 14.11.2013

SKINDICHT® SHV Neoprene® resistant to oil, dust and water  
SKINDICHT® SHV VITON® for high temperatures  
SKINDICHT® SHV VITON® resistant to oils, solvents, acids and chemicals



Good chemical resistance



Acid-resistant



Temperature-resistant

#### Application range

Sealing cone for SKINDICHT® cable glands.

#### Note

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

#### Remark

Neoprene® and Viton® are registered trademarks of DuPont de Nemours

Photographs are not to scale and do not represent detailed images of the respective products.

#### Technical Data

PG size/clear opening:	SHV 13.5/9
Inner Ø (mm):	9
Length (mm):	18,5
Pieces / PU:	100
Colour delivered:	CR: black FKM: red
Material:	CR FKM
Temperature range:	CR: -20°C to +80°C FKM: -15°C to +200°C

Product Management	Document: SKINDICHT® SHV cone seal	1 / 2
--------------------	------------------------------------	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	 <b>LAPP GROUP</b>
	<b>SKINDICHT® SHV cone seal</b>	52021271 14.11.2013



Product Management	Document: SKINDICHT® SHV cone seal	2 / 2
--------------------	------------------------------------	-------