Watertight
Gentle cable clamping
Robust
High strain relief



Optimum strain relief

Robust

Waterproof

Application range
Watertight cable gland with conical sealing element.
Pumps
Floater switches

Design
PG connection thread


Note
Counter nut to be used: SKINDICHT® SM
Suitable accessory: SKINDICHT® SHV sealing cones
Example order designation:SHV 13.5/9/913.5 = PG thread of compression screw9 = PG connection thread9 = clear opening of sealing cone

Remark
Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	SHV 21/21/18
Clamping range ØF (mm):	15,8 - 17,8
SW 1/2 mm:	30
Overall length, C (mm):	38
Thread length, D (mm):	7
Pieces / PU:	25
Caution:	The installation dimensions can be found in appendix T21
Material:	Body: nickel-plated brass Sealing cone: CR O-ring: NBR
Protection rating:	IP 68 - 10 bar
Temperature range:	-20°C to +80°C

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.



PN 0486/01_03.10
©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.