

DATA SHEET	52002530
SKINDICHT® SHV	valid from : 08.06.2006

The SKINDICHT® SHV cable gland is a water proof special gland. The special conical sealing element extends through the entire gland and thus guarantees excellent resistance to pressure and strain relief. The robust and uncomplicated design facilitates simple assembly.



The gland make-up consists of:

Gland body	nickel-plated brass
Cap	nickel-plated brass
Sealing cone	elastomere (neoprene)
Pressure cone	nickel-plated brass
Washer	galvanized steel
O – ring	elastomere (neoprene)

Technical features:

Connecting thread:	PG 7 - PG 29 in acc. to DIN 40 430
IP protection:	IP 68 at 10 bar water pressure, test in acc. to EN 60 529
Temperature range:	- 20°C to + 80 ° C

For more information please see our current catalogue.
Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.