SKINDICHT® SHV Neoprene® resistant to oil, dust and water
SKINDICHT® SHV VITON® for high temperatures
SKINDICHT® SHV VITON® resistant to oils, solvents, acids and chemicals



CE RoHS



Good chemical resistance



Acid-resistant



Temperature-resistant

Application range
Sealing cone for SKINDICHT® cable glands.

Note
Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Remark
Neoprene® and Viton® are registered trademarks of DuPont de Nemours
Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

PG size/clear opening:	SHV 9/6
Inner Ø (mm):	6
Length (mm):	14,8
Pieces / PU:	100
Colour delivered:	CR: black FKM: red
Material:	CR FKM
Temperature range:	CR: -20°C to +80°C FKM: -15°C to +200°C

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.



PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.