

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® SHV-M-VITON®	52105540 14.11.2013

For high temperatures
Resistant to oils, solvents, acids and chemicals
Watertight
High strain relief
Robust



Robust



Temperature-resistant



Waterproof

Application range

Watertight and high temperature-resistant cable gland with special conical VITON® sealing element.

Brickworks

Sewage treatment plants

Car wash sites

Design

1 fitting

2 washers

3 VITON® sealing cone

4 brass cones

5 compression screws

Note

Counter nut to be used: SKINDICHT® SM-M

Example description: SHV-M-Viton® 20/11/720 = metric connection thread 11 = PG function thread 7 = clear opening of sealing cone

Remark

Viton® is a registered trademark of DuPont de Nemours

Photographs are not to scale and do not represent detailed images of the respective products.



Product Management	Document: SKINDICHT® SHV-M-VITON®	1 / 3
--------------------	-----------------------------------	-------



U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® SHV-M-VITON®	52105540 14.11.2013

Technical Data

Article designation / size:	32 x 1,5
Clamping range ØF (mm):	19,5 - 21,8
Function thread PG:	29
SW (mm):	40 / 40
Overall length, C (mm):	44,5
Thread length, D (mm):	8
Clear opening F (mm):	22
Pieces / PU:	10
Caution:	The installation dimensions can be found in appendix T21
Material:	Body: nickel-plated brass Sealing cone: FKM O-ring: FKM
Protection rating:	IP 68 - 10 bar
Temperature range:	-15°C to +200°C

Product Management	Document: SKINDICHT® SHV-M-VITON®	2 / 3
--------------------	-----------------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® SHV-M-VITON®	52105540 14.11.2013



Product Management	Document: SKINDICHT® SHV-M-VITON®	3 / 3
--------------------	-----------------------------------	-------