

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® SRE-M	52105610 14.11.2013

Perfect seal with anti-kink protection
Optimum, low-resistance 360° screen contact
Cable-protecting strain relief
Gentle cable clamping
High degree of protection



Mechanical resistance



Optimum strain relief



Interference signals



Application range

Earthing gland with additional anti-kink protection. For applications where electrical interference fields can occur.
Moving machine parts
Conveyor and transport systems
Production lines
Measurement and control technology

Design

Metric connection thread acc. to EN 50262

Note

Counter nut to be used: SKINDICHT® SM-M
SKINDICHT® SM-PE-M counter nut should be used to ensure optimum contact with painted, anodised or powder-coated housings
Example description: SRE-M 20/13.5/9/620 = connection thread 13.5 = PG function thread 9 = clear opening of anti-kink sleeve 6 = clear opening of earthing sleeve

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINDICHT® SRE-M	1 / 3
--------------------	----------------------------	-------


U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® SRE-M	52105610 14.11.2013

Technical Data

Article designation / size:	20 x 1,5
Function thread PG:	13.5
Outer sheath clamping range ØF (mm):	9 - 11
Inner sheath clamping range (mm):	5,5 - 7
SW1/SW2 mm:	22 / 22
Overall length, C (mm):	59,5
Thread length, D (mm):	6
Clear opening earthing sleeve ØB:	7
Clear opening F (mm):	11
Pieces / PU:	25
Caution:	The installation dimensions can be found in appendix T21
On request:	Available with long connection thread
Material:	Body: nickel-plated brass Earthing sleeve: plain brass Anti-kink sleeve: CR/NBR O-ring: NBR
Protection rating:	IP 65
Temperature range:	-20°C to +80°C

Product Management	Document: SKINDICHT® SRE-M	2 / 3
--------------------	----------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® SRE-M	52105610 14.11.2013



Product Management	Document: SKINDICHT® SRE-M	3 / 3
--------------------	----------------------------	-------