

DATA SHEET	52005480
SKINDICHT® SVF	valid from : 09.06.2006

The SKINDICHT® SVF flat cable gland consists of an upper and a lower part with a special seal insert and two compression washers. The lateral sealing lips fit automatically around various cable dimensions, so that with only one seal, for each PG-size, flat cables of different outer dimensions can be sealed. Even it is possible to fit two flat cables with one gland.



The gland make- up consists of:

Gland body	nickel- plated brass
Pressure screw	nickel- plated brass
Compression washers	galvanized steel
Flat cable sealing	elastomere (neoprene)

Technical features:

Connecting thread:	PG 16 - PG 48 in acc. to DIN 40 430
Material:	nickel-plated brass
Sealing insert	neoprene
Washers:	galvanized steel
IP protection:	IP 54, test in acc. to EN 60 529
Temperature range:	- 20°C to + 80°C

For more information please see our current catalogue.

Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.