

U.I. Lapp GmbH	DATASHEET	
	SKINDICHT® SVF	52005520 14.11.2013

High mechanical stability
Lateral sealing lips fit automatically around various cable dimensions
Optimum strain relief
Large opening allows clamping of up to two flat cables



Robust

Application range

For inserting flat cables.
Conveyor systems
Pumps
Lifts
Control cabinet manufacturing

Design

PG connection thread

Note

For suitable flat cables, refer to ÖLFLEX® LIFT F for indoor applications or ÖLFLEX® CRANE F for outdoor applications
Counter nut to be used: SKINDICHT® SM

Remark

Photographs are not to scale and do not represent detailed images of the respective products.


Technical Data

Article designation / size:	PG 42
Min./max. flat cable width:	29 - 45
Min./max. cable thickness (mm):	5 - 12
SW1/SW2 mm:	57 / 54
Overall length, C (mm):	40
Thread length, D (mm):	10
Pieces / PU:	5
Caution:	The installation dimensions can be found in appendix T21
On request:	Available with long connection thread
Material:	Body: nickel-plated brass Special sealing insert: CR
Protection rating:	IP 54
Temperature range:	-20°C to +100°C



Product Management	Document: SKINDICHT® SVF	1 / 2
--------------------	--------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® SVF	52005520 14.11.2013



Product Management	Document: SKINDICHT® SVF	2 / 2
--------------------	--------------------------	-------