

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® SVF	52005530 14.11.2013

High mechanical stability
 Lateral sealing lips fit automatically around various cable dimensions
 Optimum strain relief
 Large opening allows clamping of up to two flat cables



Robust

Application range

For inserting flat cables.
 Conveyor systems
 Pumps
 Lifts
 Control cabinet manufacturing

Design

PG connection thread

Note

For suitable flat cables, refer to ÖLFLEX® LIFT F for indoor applications or ÖLFLEX® CRANE F for outdoor applications
 Counter nut to be used: SKINDICHT® SM

Remark

Photographs are not to scale and do not represent detailed images of the respective products.


Technical Data

Article designation / size:	PG 48
Min./max. flat cable width:	34 - 50
Min./max. cable thickness (mm):	5 - 12
SW1/SW2 mm:	64 / 60
Overall length, C (mm):	41,5
Thread length, D (mm):	10
Pieces / PU:	5
Caution:	The installation dimensions can be found in appendix T21
On request:	Available with long connection thread
Material:	Body: nickel-plated brass Special sealing insert: CR
Protection rating:	IP 54
Temperature range:	-20°C to +100°C



Product Management	Document: SKINDICHT® SVF	1 / 2
--------------------	--------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® SVF	52005530 14.11.2013



Product Management	Document: SKINDICHT® SVF	2 / 2
--------------------	--------------------------	-------