

DATA SHEET	52107320
SKINDICHT® SVF-M	valid from : 16.07.2009

The SKINDICHT® SVF-M, a flat cable gland made of brass with hexagonal body. The special feature of this flat cable gland is the design of the sealing lips. The lateral sealing lips fit automatically around various cable dimensions, so that flat cables of different outer dimensions can be sealed with only one seal for each PG - size. With suitable matching it is even possible to fit two flat cables with one gland.

Application range:

Switch cabinet building, conveyor systems, pumps and elevators

Note:

For suitable flat cables see ÖLFLEX® LIFT F for indoor applications or ÖLFLEX® CRANE F for outdoor applications.

Counter nut to be used SKINDICHT® SM-M.



The gland make-up consists of:

Body:	nickel plated brass
Dome nut:	nickel plated brass
Flat cable seal:	CR
Flat cable washer:	steel plate zinc plated

Technical Feature:

Connection thread:	M20 bis M63 in acc. to EN 50262
Temperaturbereich:	- 20° C up to + 100° C

Norm references:



For more information please see our current catalogue.

Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

elaborated by: TE-VZ: M. Steinberg	Document: DB52107320EN	page 1 of 1
---------------------------------------	------------------------	-------------