

DATA SHEET	53015410
SKINTOP® BT / BTR	valid from : 04.09.2006

SKINTOP® BT with the plastic trumpet-shaped cable entry is used as a guard for flexible cables and leads. It is particularly used for flexible cables on electrical engineering equipment, and machine parts as well as in many applications of the instrument industry.



The gland make-up consists of:

Gland body with lamellar design
Cap with conical guard
Seal insert

plastic polyamide- based (UL-94-V2)
plastic polyamide- based (UL-94-V2)
elastomere

Technical features:

Connecting thread:

PG 9 to PG 21 in acc. to DIN 40 430

Special thread:

multi-start trapezoidal thread

IP protection:

IP 68 - 5 bar, test in acc. to EN 60 529

Strain relief:

in acc. to DIN VDE 0619

Temperature range:

- 20°C up to + 80°C in static strain

Conical guard:

in acc. to VDE 0730

For more information please see our current catalogue.

Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.