Easy insertion of several cables into one gland
Higher packing density allows smaller part construction



Assembly time

Reliability

Temperature-resistant

Application range

For use in SKINTOP® cable glands.
A sealing ring with several holes is used in place of the inner sealing insert.

Note

IP 68 can be achieved when all openings are closed and all bores are optimally occupied, i.e. when using cables with nominal diameter and/or SKINTOP® DIX-DV sealing plugs

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	DIX 29390
PG size:	29
Number of cables x cable Ø:	3 x 9
Pieces / PU:	50
Colour delivered:	natural
Material:	Silicone
Protection rating:	IP 54
Temperature range:	-40°C to +100°C

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.