

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® GMP-GL	53019080 14.11.2013

Glass fibre-reinforced for maximum mechanical stability
Supporting surface for spanner means scratches on the housing are avoided



Assembly time



Temperature-resistant



Variety of approval certifications



Application range

For locking SKINTOP® cable glands in boreholes without thread.

Design

PG connection thread

Norm references / Approvals

UL File Nr. E79903

Note

UL approval only when used with the UL-approved SKINTOP® polyamide cable glands
Designed for use with SKINTOP® ST(R)

Remark


Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	GMP-GL 42
SW (mm):	65
Pieces / PU:	25
On request:	Available without collar (without surface for assembling tool)
Colour delivered:	Silver grey (RAL 7001) Light grey (RAL 7035) Black (RAL 9005), UV-resistant
Material:	Polyamide, glass fibre-reinforced
Temperature range:	-20°C to +100°C

Product Management	Document: SKINTOP® GMP-GL	1 / 2
--------------------	---------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® GMP-GL	53019080 14.11.2013



Product Management	Document: SKINTOP® GMP-GL	2 / 2
--------------------	---------------------------	-------