

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® GMP-HF-M	53119270 14.11.2013

Halogen-free
Extremely flame-retardant according to UL 94 V0
Self-extinguishing, no dripping



Halogen-free



Assembly time



Temperature-resistant



Variety of approval certifications

Info

Cable gland for railway applications- Fire protection on railway vehicles Approval according to DIN EN 45545-2:2013

Application range

For locking SKINTOP® cable glands in boreholes without thread.

Airports

Tunnel construction

Underground railways

Public buildings

Design

Metric connection thread acc. to EN 50262

Note

Designed for use with SKINTOP® ST-HF-M

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	63 x 1,5
SW (mm):	75
PU:	25
Colour delivered:	Light grey (RAL 7035)
Material:	Polyamide UL 94V-0 - halogen-free
Temperature range:	-20°C to +100°C

Product Management	Document: SKINTOP® GMP-HF-M	1 / 1
--------------------	-----------------------------	-------