

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® KR-M ATEX plus blue	54115435 04.04.2014


For the benefits, refer to SKINTOP® K-M ATEX plus blue



Mechanical resistance



Oil & Gas



Optimum strain relief



Reliability



Variety of approval certifications

Application range

With reducing seal insert, to seal cables with smaller outer diameters.

Design

Metric connection thread acc. to EN 50262

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINTOP® KR-M ATEX plus blue	1 / 3
--------------------	--	-------


U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® KR-M ATEX plus blue	54115435 04.04.2014

Technical Data

Article designation / size:	KR-M 25 ATEX plus blue
Clamping range ØF (mm):	6-13
Thread M:	25 x 1.5
SW (mm):	30
Overall length, C (mm):	35 - 40
Thread length, D (mm):	10
Pieces / PU:	25
Caution:	Refer to the instruction leaflet for the installation dimensions and torques
Approvals:	CE 0637 Ex II 2G Ex eb IIC Ex II 1D Ex ta IIIC IECEx IBE 13.0027X
Colour delivered:	Blue (RAL 5015)
Material:	Body: special polyamide Seal: special elastomer O-ring: CR
Tests:	DIN EN 60079-0 DIN EN 60079-7
Protection rating:	IP 68 - 10 bar
Temperature range:	-20°C to +80°C

Product Management	Document: SKINTOP® KR-M ATEX plus blue	2 / 3
--------------------	--	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® KR-M ATEX plus blue	54115435 04.04.2014



Product Management	Document: SKINTOP® KR-M ATEX plus blue	3 / 3
--------------------	--	-------