Permanent and secure sealing for areas with risks of explosion
Easy to assemble
High degree of protection




Assembly time

Reliability

## Application range
SKINTOP® SDV-M is used together with SKINTOP® MS-M ATEX, MS-M ATEX BRUSH or SKINTOP® K-M ATEX plus (blue).
Equipment group II / Category 2G+1D

## Note
Outside areas with a risk of explosion, also suitable for use in combination with SKINTOP® ST-M and SKINTOP® MS-M

## Remark
Photographs are not to scale and do not represent detailed images of the respective products.

## Technical Data

| | |
|---|---|
| Article designation / size: | 40 ATEX |
| Visible height (mm): | SDV-M ATEX 4 |
| Pieces / PU: | 25 |
| Caution: | Refer to the instruction leaflet for the installation dimensions and torques |
| Material: | CR |
| Protection rating: | IP 68 - sizes M12, M16, M20, M25, M32<br>IP 66 - sizes M40, M50, M63 |
| Temperature range: | -30°C to +70°C<br>Short-term: up to +90°C |



PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.