

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® SDV-M ATEX	54113062 04.04.2014

Permanent and secure sealing for areas with risks of explosion
Easy to assemble
High degree of protection



Assembly time



Reliability



Application range

SKINTOP® SDV-M is used together with SKINTOP® MS-M ATEX, MS-M ATEX BRUSH or SKINTOP® K-M ATEX plus (blue).
Equipment group II / Category 2G+1D

Note

Outside areas with a risk of explosion, also suitable for use in combination with SKINTOP® ST-M and SKINTOP® MS-M

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	50 ATEX
Visible height (mm):	SDV-M ATEX 4,5
Pieces / PU:	10
Caution:	Refer to the instruction leaflet for the installation dimensions and torques
Material:	CR
Protection rating:	IP 68 - sizes M12, M16, M20, M25, M32 IP 66 - sizes M40, M50, M63
Temperature range:	-30°C to +70°C Short-term: up to +90°C

Product Management	Document: SKINTOP® SDV-M ATEX	1 / 1
--------------------	-------------------------------	-------