

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® SDVR-M ATEX	54113043 04.04.2014

For the benefits, refer to SKINTOP® SDV-M ATEX



Assembly time



Reliability



Application range

SKINTOP® SDVR-M is used together with SKINTOP® MSR-M ATEX or SKINTOP® KR-M ATEX plus (blue).
Equipment group II / Category 2G+1D

Note

Outside areas with a risk of explosion, also suitable for use in combination with SKINTOP® STR-M and SKINTOP® MSR-M

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	32 ATEX
Visible height (mm):	SDVR-M ATEX 5,5
PU:	25
Caution:	Refer to the instruction leaflet for the installation dimensions and torques
Material:	CR
Protection rating:	IP 68
Temperature range:	-30°C to +70°C Short-term: up to +90°C

Product Management	Document: SKINTOP® SDVR-M ATEX	1 / 1
--------------------	--------------------------------	-------