

U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINTOP® NPT</b>	53016060 14.11.2013

Conical NPT thread  
 Permanent vibration protection  
 Optimum strain relief  
 Wide, variable clamping ranges  
 Maximum reliability




Good chemical resistance



Maximum vibration protection



Mechanical resistance



Optimum strain relief



Variety of approval certifications



### Application range

Used in areas where cables and wires need to be safely inserted into housings  
 Machine and equipment manufacturing  
 Automation technology  
 Devices  
 Housings

### Design

NPT connection thread acc. to ANSI B1.20.2 - 1983

### Design

SKINTOP® STR NPT is equipped with a reduction seal insert to seal cables and wires with small outer diameters.

### Norm references / Approvals

UL File Nr. E79903

### Note

Refer to SKINTOP® PG accessories for suitable accessories. Note that SKINTOP® GMP-GL counter nut is not compatible with this model.

3/8" = PG9

1/2" = PG13.5

3/4" = PG21

1" = PG29

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINTOP® NPT	1 / 3
--------------------	------------------------	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	 <b>LAPP GROUP</b>
	<b>SKINTOP® NPT</b>	<b>53016060</b> <b>14.11.2013</b>

### Technical Data

Article designation / size:	ST 1 NPT"
Clamping range ØF (mm):	19 - 25,4
SW (mm):	42
Overall length, C (mm):	60
Thread length, D (mm):	15
Pieces / PU:	25
Colour delivered:	Silver grey (RAL 7001) Black (RAL 9005), UV-resistant
Material:	Body: Polyamide Seal: CR
Protection rating:	IP 68 - 5 bar
Temperature range:	-20°C to +80°C

Product Management	Document: SKINTOP® NPT	2 / 3
--------------------	------------------------	-------

U.I. Lapp GmbH	<b>DATASHEET</b>	 <b>LAPP GROUP</b>
	<b>SKINTOP® NPT</b>	<b>53016060</b> <b>14.11.2013</b>



Product Management	Document: SKINTOP® NPT	3 / 3
--------------------	------------------------	-------