

U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINTOP® STR-M</b>	53017310 14.11.2013

For the benefits, refer to SKINTOP® ST-M



Wide clamping range




Maximum vibration protection



Mechanical resistance



Assembly time



Optimum strain relief



Temperature-resistant



Variety of approval certifications

### Info

Now with IP 69 K approval! Proven to withstand the most demanding cleaning procedures for industrial machinery with high-pressure cleaners and hot water!

### Application range

With reducing seal insert, to seal cables with smaller outer diameters.

### Design

Metric connection thread acc. to EN 50262

### Norm references / Approvals

UL File Nr. E79903

### Note

Refer to SKINTOP® metric accessories for suitable accessories

Counter nut to be used: SKINTOP® GMP-GL-M

SKINTOP® STR M ISO types have an extra-long connection thread

SKINTOP® STR M ISO versions with extra-long connection thread, see table, no DNV approval

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINTOP® STR-M	1 / 3
--------------------	--------------------------	-------


U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINTOP® STR-M</b>	<b>53017310</b> <b>14.11.2013</b>

### Technical Data

Article designation / size:	STR M 16 x 1,5
Clamping range ØF (mm):	2-6
SW (mm):	19
Overall length, C (mm):	40
Thread length, D (mm):	12
Pieces / PU:	100
Caution:	Refer to Appendix T21 for the installation dimensions and torques
Colour delivered:	Silver grey (RAL 7001) Light grey (RAL 7035) Black (RAL 9005), UV-resistant
Material:	Body: Polyamide Seal: CR
Tests:	GGVS: TÜ.EGG.020-95
Protection rating:	IP 68 - 5 bar IP 69 K
Temperature range:	Fixed: -40°C to +100°C Dynamic: -20°C to +100°C

Product Management	Document: SKINTOP® STR-M	2 / 3
--------------------	--------------------------	-------

U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINTOP® STR-M</b>	53017310 14.11.2013



Product Management	Document: SKINTOP® STR-M	3 / 3
--------------------	--------------------------	-------