

D-SUB HIGH DENSITY

Crimp Contacts – Screw machine design – For wire size AWG 22




RoHS compliant – CSA listed, File No.:LR115001 –UL listed, File No.:E202784

DESCRIPTION


- For wire size **AWG 22**
- Loose contacts, in poly bag (500 pieces)
- Quality class 3 (also available in quality class 1)

FEMALE CONTACT


Standard version



Closed entry version



MALE CONTACT



Technical Data

Contact material	Precision machined contacts	Brass
Contact plating		Gold plated over nickel
Temperature range		-55°C to +125°C
Rated current for AWG 24		3 A
Contact resistance		≤ 10 mΩ

ORDER DATA

FEMALE CONTACTS

Contact type	Part Number
AWG 22 / Loose contact	162 A 18419 X
AWG 22 / Loose contact closed entry version	16-000693

MALE CONTACTS

Contact type	Part Number
AWG 22 / Loose contact	161 A 18009 X