



OMNITRONIC DX 3-way speaker

Rugged full-range speaker-system

- 3-way party speaker-system for disco and rock music
- 20 cm woofer (8"), piezo, horn
- High-quality horn for smooth mid-range
- Piezo super-tweeters for powerful treble
- Very high durability

No. 11037055	DX-822
No. 11037061	DX-1022
No. 11037071	DX-1222
No. 11037081	DX-1522
No. 11037085	DX-2022
No. 11037087	DX-2222
No. 11037091	DX-2522

Technical specifications:

Device:	DX-822	DX-1022	DX-1222	DX-1522	DX-2022	DX-2222	DX-2522
Rated power:	150 W RMS	200 W RMS	300 W RMS	400 W RMS	400 W RMS	500 W RMS	600 W RMS
Program power:	300 W	400 W	600 W	800 W	800 W	1000 W	1200 W
Components:	20 cm woofer (8"), piezo, horn	25 cm woofer (10"), piezo, horn	30 cm woofer (12"), piezo, horn	38 cm woofer (15"), piezo, horn	2 x 25 cm woofer (2 x 10"), piezo, horn	2 x 30 cm woofer (2 x 12"), piezo, horn	2 x 38 cm woofer (2 x 15"), 2 piezos, horn
Connections:	2 Speaker sockets	2 Speaker sockets	2 Speaker sockets	2 Speaker sockets	2 Speaker	2 Speaker sockets	2 Speaker sockets
Sensitivity:	93 dB (1 W, 1 m)	95 dB (1 W, 1 m)	96 dB (1 W, 1 m)	97 dB (1 W, 1 m)	96 dB (1 W, 1 m)	99 dB (1 W, 1 m)	101 dB (1 W, 1 m)
Impedance:	8 ohms	8 ohms	8 ohms	8 ohms	8 ohms	8 ohms	8 ohms
Frequency range:	50 - 18000 Hz	50 - 18000 Hz	30 - 18000 Hz	30 - 18000 Hz	45-20000 Hz	30 - 18000 Hz	30 - 18000 Hz
Dimensions (H x W x D):	400 x 320 x 280 mm	465 x 360 x 310 mm	520 x 360 x 310 mm	655 x 475 x 355 mm	780 x 350 x 330 mm	910 x 375 x 360 mm	1060 x 500 x 405 mm
Weight:	9 kg	9.5 kg	13 kg	16 kg	15 kg	18 kg	40 kg

OMNITRONIC BX Subwoofer

Powerful subwoofer

- 300-600 W RMS
- Passive crossover
- Good extension for DX, DS, TX or TMX



No. 11037705	BX-1250
No. 11037711	BX-1550
No. 11037731	BX-1850
No. 11037745	BX-2250
No. 11037751	BX-2550

Technical specifications:

Device:	BX-1250	BX-1550	BX-1850	BX-2250	BX-2550
Rated power:	300 W RMS	400 W RMS	600 W RMS	400 W RMS	600 W RMS
Program power:	600 W	800 W	1200 W	800 W	1200 W
Components:	30 cm woofer (12")	38 cm woofer (15")	45 cm woofer (18")	2 x 30 cm woofer (2 x 12")	2 x 38 cm woofer (2 x 15")
Connections:	2 Speaker sockets	2 Speaker sockets	2 Speaker sockets	2 Speaker sockets	2 Speaker sockets
Sensitivity:	96 dB (1 W, 1 m)	97 dB (1 W, 1 m)	99 dB (1 W, 1 m)	98 dB (1 W, 1 m)	101 dB (1 W, 1 m)
Impedance:	8 ohms	8 ohms	8 ohms	8 ohms	8 ohms
Frequency range:	20-400 Hz	20-300 Hz	20-300 Hz	20-400 Hz	15-300 Hz
Dimensions (H x W x D):	480 x 390 x 320 mm	585 x 470 x 455 mm	675 x 545 x 455 mm	745 x 390 x 320 mm	900 x 465 x 455 mm
Weight:	12 kg	18 kg	29 kg	18 kg	27 kg