



PAS-210



PAS-208

**OMNITRONIC PAS 100V PA speaker system**

Universal speaker system

- 2-way bass reflex system
- Constant directivity horn with coil-driver
- Higher volumes as with conventional 100 V systems

No. 80710460 .....	PAS-208
No. 80710465 .....	PAS-210

**Technical specifications:**

Device:	PAS-208-100V	PAS-210-100V
Input voltage:	100 V	100 V
Rated power:	150 W RMS	200 W RMS
Program power:	300 W	400 W
Connection:	open wires (1 m)	open wires (1 m)
Components:	20 cm woofer (8"), 2.5 cm horn (1")	25 cm woofer (10"), 2.5 cm horn (1")
Sensitivity (1 W/ 1 m):	97 dB	97 dB
Max. SPL (1 m):	122 dB	123 dB
Frequency range:	70 Hz - 20 kHz	60 Hz - 20 kHz
Dispersion angle (1 kHz):	90° x 40°	50-100° x 55°
Dimensions (H x W x D):	400 x 250 x 250 mm	530 x 325 x 295 mm
Weight:	11 kg	19.5 kg



WPS

**OMNITRONIC WP/WPS PA wall speaker**

Universal wall speaker black

- 2-way system with 100 V transformer
- Multi-step power selector (WPS only)
- For indoor amplifying systems

No. 80710506 .....	WP-3S, black
No. 80710507 .....	WP-3W, white
No. 80710510 .....	WP-4S, black
No. 80710511 .....	WP-4W, white
No. 80710520 .....	WP-5S, black
No. 80710521 .....	WP-5W, white
No. 80710530 .....	WP-6S, black
No. 80710531 .....	WP-6W, white

No. 80710508 .....	WPS-3S, black
No. 80710509 .....	WPS-3W, white
No. 80710512 .....	WPS-4S, black
No. 80710513 .....	WPS-4W, white
No. 80710522 .....	WPS-5S, black
No. 80710523 .....	WPS-5W, white
No. 80710532 .....	WPS-6S, black
No. 80710533 .....	WPS-6W, white

**Technical specifications:**

Device:	WP-3	WP-4	WP-5	WP-6	WPS-3	WPS-4	WPS-5	WPS-6
Input voltage:	100 V	100 V	100 V	100 V	100 V	100 V	100 V	100 V
Rated power:	15 W RMS	20 W RMS	30 W RMS	40 W RMS	2.5/5/10/15 W RMS	2.5/5/10/20 W RMS	3.75/7.5/15/30 W RMS	5/10/20/40 W RMS
Sensitivity (1 W/ 1 m):	88 dB, ±3 dB	89 dB, ±3 dB	89 dB, ±3 dB	88 dB, ±3 dB	88 dB, ±3 dB	89 dB, ±3 dB	89 dB, ±3 dB	88 dB, ±3 dB
Max. SPL (1 m):	98 dB	101 dB	103 dB	105 dB	98 dB	101 dB	103 dB	105 dB
Frequency range:	100 Hz - 20 kHz	100 Hz - 20 kHz	100 Hz - 20 kHz	70 Hz - 20 kHz	100 Hz - 20 kHz	100 Hz - 20 kHz	100 Hz - 20 kHz	70 Hz - 20 kHz
Dimensions (H x W x D):	197 x 130 x 115 mm	215 x 170 x 150 mm	242 x 182 x 162 mm	284 x 215 x 190 mm	197 x 130 x 115 mm	215 x 170 x 150 mm	242 x 182 x 162 mm	284 x 215 x 190 mm
Weight:	1.7 kg	2.3 kg	2.5 kg	3.5 kg	1.8 kg	2.2 kg	2.6 kg	3.5 kg