



OMNITRONIC Gooseneck black XLR/XLR, 47cm

Flexible connection piece

- E. g. for putting a microphone on an XLR socket at the mixer
- Fully wired
- Length: 47 cm

No. 60006105..... 47cm, black



EUROLITE Flexilight LED table lamp battery-powered

LED gooseneck table lamp with magnetic base

- Battery-powered for universal use
- 360° rotatable head
- Magnetic base for easy fixation
- Integrated dimmer

No. 80702201

Technical specifications:

Power supply:	3 x 1.5 V mignon batteries (type AA)
Power consumption:	1.3 W
Number of LEDs:	4
Dimensions (LxWxH):	200 x 40 x 360 mm
Weight:	300 g



EUROLITE Flexilight LK LED lamp head

Spare LED head for battery-powered LED table lamp

- Round spare head with halogen lamp 12V/5W
- Seashell spare head with bayonet lamp 12V/5W
- White spare LED head for table lamp

Technical specifications LK-1, LK-2:

Power supply:	12 V UC
Power consumption:	5 W

No. 80702215.....LK-1, Round spare head with halogen lamp 12V/5W
 No. 80702216...LK-2, Seashell spare head with bayonet lamp 12V/5W
 No. 80702203...LK-6, White spare LED head for table lamp 80702201



EUROLITE Flexilight LED gooseneck, XLR

LED gooseneck light with XLR plug

- LED head is equipped with extremely bright 4 LEDs
- 360° degree rotatable head light
- XLR plug

No. 80702220

Technical specifications:

Power supply:	12 V DC, 100 mA
Power consumption:	2 W
Number of LEDs:	4
Length:	370 mm
Weight:	100 g



EUROLITE Flexilight LED gooseneck, BNC

LED gooseneck light with BNC plug

- LED head is equipped with extremely bright 4 LEDs
- 360° degree rotatable head light
- BNC plug

No. 80702222

Technical specifications:

Power supply:	12 V DC, 100 mA
Power consumption:	2 W
Number of LEDs:	4
Length:	370 mm
Weight:	100 g



EUROLITE Flexilight LED gooseneck, XLR, 90°

LED gooseneck light with angled 3-pin XLR plug

- LED head is equipped with extremely bright 4 LEDs
- 360° degree rotatable head light
- Including XLR plug 90°

No. 80702225

Technical specifications:

Power supply:	12 V DC, 100 mA
Power consumption:	2 W
Number of LEDs:	4
Length:	390 mm
Weight:	100 g



EUROLITE Flexilight LED table lamp

LED gooseneck table lamp

- With dimming function
- LED head is equipped with extremely bright 4 LEDs
- 360° degree rotatable head light

No. 80702227

Technical specifications:

Power supply:	230 V AC, 50 Hz ~ via 7 V DC, 150 mA power unit
Power consumption:	2 W
Number of LEDs:	4
Length:	370 mm
Weight:	300 g



EUROLITE Flexilight LED racklight with 2 lamps

Illumination unit for rack installation - Useful tool for every DJ booth

- 483 mm front panel for rack installation
- 2 LED gooseneck lamps
- On/off switch and brightness control

No. 80702235

Technical specifications:

Power supply:	7 V DC, 150 mA
Power consumption:	4 W
Number of LEDs:	8
Length:	370 mm
Weight:	650 g