



Bulk Cables										
Cable	Type	Conductor Area (single cond., mm ²)	AWG	Conductor Structure (strand cond., mm)	Resistance (Ohm/km)	Capacitance Cond-cond (pF/m)	Shielding	Jacket	Colors	Outer Diam. OD (mm)
intro cable 1	Microphone	0,22	24	28 x 0,1	80	80	Spiral shield	PVC mat	black, white	5,9
intro cable 2	Microphone	0,22	24	28 x 0,1	80	80	Spiral shield	PVC mat	black, white	4,3
intro cable 3	Twin Microphone	0,22	24	28 x 0,1	80	80	Spiral shield	PVC mat	black, white	4,3
intro cable 4	Twin Microphone	0,22	24	28 x 0,1	80	90	Spiral pair shield	PVC mat	black, white	4,6
intro cable 5	Guitar/Instrument	0,22	24	7 x 0,2	80	140	Spiral shield	PVC mat	black	5,9
intro cable 6	Audio Multicore (8 x 2)	0,22	24	7 x 0,2	79	72	Pair screen foil PT/AL	PVC mat	black	15
intro cable 7	Loudspeaker	1,5	16	48 x 0,2	12	200	-	PVC mat	black	7
intro cable 8	Loudspeaker	2,5	14	48 x 0,2	7	200	-	PVC mat	black	7,8
intro cable 9	AES/EBU DMX (110 Ω)	0,15	26	19 x 0,1	120	75	Spiral shield	PVC mat	black	3,5
intro cable 10	Audio Multicore (4 x 2)	0,22	24	7 x 0,2	79	72	Pair screen foil PT/AL	PVC mat	black	7,8
intro cable 11	Audio Multicore (8 x 2)	0,22	24	7 x 0,2	79	72	Pair screen foil PT/AL	PVC mat	black	10,6
intro cable 12	Audio Multicore (12 x 2)	0,22	24	7 x 0,2	79	72	Pair screen foil PT/AL	PVC mat	black	12,3
intro cable 13	Audio Multicore (16 x 2)	0,22	24	7 x 0,2	79	72	Pair screen foil PT/AL	PVC mat	black	13,5
intro cable 14	Audio Multicore (20 x 2)	0,22	24	7 x 0,2	79	72	Pair screen foil PT/AL	PVC mat	black	14,7
intro cable 15	Audio Multicore (24 x 2)	0,22	24	7 x 0,2	79	72	Pair screen foil PT/AL	PVC mat	black	16
intro cable 16	Audio Multicore (28 x 2)	0,22	24	7 x 0,2	79	72	Pair screen foil PT/AL	PVC mat	black	17,2
intro cable 17	Audio Multicore (32 x 2)	0,22	24	7 x 0,2	79	72	Pair screen foil PT/AL	PVC mat	black	17,9