



ALLNET

ALL-MC102-SC-MM

Media Converter 10/100BaseTX to 100BaseFX

- 1x 10/100BaseTX Ethernet TP Port; 1x 100BaseFX Ethernet Fiber Port
- TP Port can support Half/Full-Duplex, Auto-MDI/MDI-X and Auto-Negotiation
- 1x 100BaseFX Fiber Port support Multi Mode SC
- Ethernet 802.3x Flow Control

Art.-Nr.102458

Note: Product specification is subject to change without notice.

www.allnet.de



Item	Spezification
Standards:	IEEE 802.3 10BaseT IEEE 802.3u 100BaseTX/100BaseFX IEEE 802.3x FLOW Control
Features:	1x 10/100BaseT with RJ-45 Connector 1x 100BaseFX with Fiber Connector MM,SC
Data Transfer Rate:	Ethernet: 10Mbps/Half-Duplex; 20Mbps/Full-Duplex Fast Ethernet: 100Mbps/Half-Duplex; 200Mbps/Full-Duplex
Transmission Media:	10BaseT Cat. 3, 4, 5 UTP/STP, up to 100 m 100BaseTX Cat. 5 UTP/STP, up to 100 m 100BaseFX: 50/125µm or 62.5/125µm Multi Mode SC-Type Fiber optic cable, up to 2 km
Led Indicators:	Power on Per Port:(TX): Link/Act, Speed, FDX/COL ; (FX): Link/Act, FDX/COL
Power Requirement:	DC 5V/2A external Power Supply included, Replace PSU = Part NO: 140858
Power Consumption:	2,5 Watts (Max)
Dimensions:	94 × 71 × 26 mm (L x W x H)
Weight:	230g (only MC)
Environment:	Temperature operating: 0 ~ 50 °C Humidity operating: 10% ~ 90% (non-condensing) Temperature storage: -20 ~ 70 °C Humidity storage: 10% ~ 90% (non-condensing)
Certifications:	CE