



### SPECIFICATIONS

<b>Minimum No Load Voltage:</b>	1.55 V
<b>Minimum On Load Voltage:</b>	.84V on 220hms at 1000
<b>Minimum Life</b>	670 H 15k Ohms Hr/Day 1.2 V
<b>Rated Capacity</b>	70 mAh on 15kOhms to 1.2V
<b>Volume</b>	.28 cm <sup>3</sup>
<b>Weight</b>	1.27g

Physical Size in mm	Max	Min
Height/Length	3.05	2.75
Width/Diameter	11.6	11.25
Depth		

### Typical Discharge Characteristics

