



DIO FLEX PLATE GU10 Design by CDC



120VAC



Socket/Bulb:
GU10/GU10 (excl.)
50W max.

Versions:
chrome

Art. No.:
8146692U

Material:
Aluminum

Dimensions:
Head-Ø/L: 6.2/1.5 in.
Flexible arm-L: 15.7 in.
Canopy-Ø: 4.5 in.
Total-L: 15.7 in.

Recommended bulb:
GU10/PAR16 HALOGEN 120V
50W 50° 2700K, 580cd
575510U



Recommended bulb:
GU10/PAR16 LED 120V 6W 25°
3000K 325lm, 793362U
GU10/PAR16 LED 120V 6W
40° 3000K 325lm, 793372U



SLV Lighting North America, Inc.

5731 Benjamin Center Dr. • Tampa, FL 33634

Main line: (813) 349-1900 • Fax line: (813) 349-1907 • www.slvlighting.com