

*description*

**FF 15 P A 230 U N R 5 C 1 O -SXX**

*description*

**FAMILY FF**

**DIMENSION CODE**

**08** - 106.5 x 106.5    **12** - 150 x 150

**13** - 204 x 204        **15** - 250 x 250

**20** - 325 x 325

**FAN SIZE**

**P** = small        **M** = medium        **G** = large

**GE** = large with plastic adaptor        **()** = standard

**VOLTAGE**    **A** = a.c. voltage    **D** = d.c. voltage

**RATED VOLTAGE**

**115** = 115 Vac.    **230** = 230 Vac.    **400T** = 400 3~

**24** = 24 Vdc.        **48** = 48 Vdc.

**COLOUR**

**R** = grey RAL 7032    **U** = grey RAL 7035    **N** = black RAL 9005

**CUSTOM SERIES**

**SXX** = custom version

**FILTER**

**()** = with filter mat        **O** = without filter mat

**VERSION**

**EMC**

**C** = EMC shielded

**IP PROTECTION**

**5** = IP55

**AIR FLOW DIRECTION**

**()** = standard flow        **R** = reverse flow

**FAN SUPPLIER**

**N** = NMB internal fan    **F** = Fandis internal fan

**E** = Ecofit internal fan