

Wireless Room Thermostat, surface mount



Product ref: 132030

PRODUCT FEATURES



- Wireless room thermostat enables time-controlled regulation of room temperature in connection with one or more HomeMatic Wireless Radiator Thermostats (HM-CC-RT-DN)
- The room thermostat measures the temperature and humidity and cyclically transmits the data to the radiator thermostat - the room temperature can be regulated precisely and quickly
- Setpoint temperature in the room can be specified precisely (to the nearest 0,5°) via adjustment wheel
- Flexible due to individual adjustment of week programmes and configuration directly on the device
- Can be individually tailored to personal routines thanks to the freely programmable heating phases
- Boost function for heating up the radiator quickly and briefly
- Large display shows setpoint and actual temperature as well as humidity
- Can be easily mounted with supplied adhesive stripes
- Integration into multi-gang frames or frames of other manufacturers (e.g. Berker, ELSO, Gira, merten, JUNG) possible
- Electronic radiators can be controlled in connection with directly taugh-in switching actuators

TECHNICAL DATA

Supply voltage:	2 x 1.5 V LR03/micro/AAA
Battery lifetime:	approx. 1 year (typ.)
Current consumption:	40 mA (max.)
Typ. open area RF range:	> 100 m
Radio frequency:	868.3 MHz
Receiver class:	SRD Class 2
Degree of protection:	IP20
Protection class:	III
Dimensions (W x H x D)	
Without frame	55 x 55 x 20 mm
Incl. frame:	86 x 86 x 21.5 mm
Weight:	74 g (not incl. batteries)

LOGISTIC DATA

Product ref.:	132030
EAN code:	4047976320301
Short description:	HM-TC-IT-WM-W-EU
Packaging unit:	48
Size (incl. packaging):	100 x 100 x 50 mm
Weight (incl. packaging):	154 g

PACKAGING CONTENT

Wireless Room Thermostat
2 x LR03/micro/AAA batteries
Mounting accessories (2 x adhesive stripes, 2 x plugs, 2 x screws)
Operating manual in G and E

Subject to technical changes.