

Art. 90319



Description

H4 Bulb Holder

Design Voltage

12 volts DC

Max Load

10 amps

Contact Resistance

50m Ω max

Insulation Resistance

500 Volts D.C. 100M Ω min

Dielectric Strength

1500 Volts A.C., 1 Minute

Operating Temperature

-25°C ~ +70°C

Operational Life

5000 hours approx

Socket
P43t

Betriebsspannung
12 V

Bauart
H4, R2